



Centre for concepts in mechatronics
Email: info@ccm.nl
Website: www.ccm.nl
Phone: +31 40 2635000

Digital Metal Hoganas

Contact via: http://www.hoganas.com/en/business-areas/digital-metal/get-in-touch/
Website: www.hoganas.com/digitalmetal

Transcenda

Email: euinfo@transcenda.com
Website: www.transcenda.com
Phone: +44 (0) 1954 234300

Swerea IVF

Email: info@swerea.se
Website: www.swerea.se
Phone: +46 (0)31 7066000

TNO

Contact name: Frits Feenstra
Email: Frits.Feenstra@tno.nl
Website: www.tno.nl
Phone: +31 88 8660866



UNIVERSITY OF BIRMINGHAM

Contact name: Debajyoti Bhaduri
Email: D.Bhaduri@bham.ac.uk
Website: www.birmingham.ac.uk
Phone: +44 (0) 121 414 4161

The technical objective of Hyproline is to design, implement and validate a flexible high performance manufacturing line for serial fabrication of customized high quality metal parts that combines innovatively component technologies for net shape manufacture, direct write / structuring, inspection and intelligent automation. By further developing the manufacturing processes itself as well as by research and application work on materials, pre and post treatment of the parts produced and supporting software Hyproline adds capabilities to commercially available manufacturing systems, in terms of speed, product quality and versatility.


www.hyproline.eu



Hyproline has received funding from the European Union's Seventh Framework Programme for research, technological development and demonstration under grant agreement no 314685


High Performance Production Line for Small Series Metal Parts

HYPROLINE



Hybrid platform

- 100 building / machining platforms
- 100 separate parts in operation
- High speed: 1m/s nominal (capable of 2m/s)
- Robotic high speed removal / placement of building platforms
- Modules for polymer 3D printing, curing, measurement and laser machining



AM Components

- Products manufactured at 20µm resolution.
- Low initial surface roughness
- Consistent surface quality
- Printing in steel, copper, titanium



Laser Machining

- On the fly laser machining
- Perform both ablation and polishing
- Improvement in surface roughness from 3µm to below 0.5µm.
- Use of inert gases to improve surface finish
- Non-contact process
- Preserve sharp features





Fig. 9 Surface roughness (a) 3D printed SS 316 part and (b) after laser polishing

Measurement

- On the fly 3D measurement at reduced speed
- Uses Micro-Epsilon Scancontrol laser line scanner
- measurement volume of 4cm x 8cm x 4cm
- Resolution of 20 micrometers in X and Y



Software

- Software for inspection and analysis of products
- Curved facet slicing for higher accuracy printing
- Comparisons between point clouds and nominal geometry.
- Creation of difference volumes and hatching patterns

